

## EVG 80/1.5

**Type** Electronic transformer for high-voltage

luminous discharge tubes according to

EN 50107.

Suitable for indoor and outdoor systems. Limited suitability for flash operation.

Weight 0.750 kg

Radio

interference According to

VDE 0875, Part 2A1 (EN 55015) suppression

Ambient temperature range: -25 to +55°C <u>Temperatures</u>

Temperature limit: +70°C

(max. ambient temp. that the EVG is able to withstand for a short period of time without being destroyed)

Polystyrene shell Housing

Standard colour: white

Sealing compound: polyurethane (black)

Class of protection

IP 67 Degree of protection

**Primary Data** 

230 V, +/- 10 %, 50 / 60 Hz Mains voltage

Depends on the connected tube load; Current consumption

max. 0.60 A

cos phi 0.95

**Protective Equipment** 

Integrated 1 A melting fuse offering Safety fuse

protection against internal short circuits

(acc. to EN 50107) integrated in the Earth leakage trip

transformer

(acc. to EN 50107) integrated in the Open circuit protection

transformer

## Caution:

The installation instructions must be observed when using the transformer!

## **Secondary Data**

1.500 V with 80 mA constant current, symmetrical alternating current, loaddependent operating frequency, 16 - 20 kHz, centrally earthed secondary winding.

Secondary current tolerance:

-5/+10 % (of rated value)

Suitable for blue discharge tubes.


Only partly suitable for red discharge tubes due to an occasional jelly bean effect.

## Connectable tube lengths (in metres):

Blue discharge (outdoor)									
Diameter	10	12	15	18	20	22			
1 Syst.	1.6	2.0	2.5	2.9	3.1	3.4			
2 Syst.	1.2	1.5	1.8	2.1	2.3	2.5			
3 Syst.	8.0	1.0	1.2	1.4	1.5	1.7			

Blue discharge (indoor)									
Diameter	10	12	15	18	20	22			
1 Syst.	2.0	2.5	3.0	3.5	3.8	4.1			
2 Syst.	1.6	2.0	2.4	2.8	3.0	3.3			
3 Syst.	1.2	1.5	1.8	2.1	2.3	2.5			

The values given represent the maximum connectable tube lengths which must not be exceeded. Shorter tube lengths, however, may be connected without any restrictions. The tube lengths are calculated on the basis of the 'Filling Pressure Recommendations for Fluorescent Tubes' published by the German Fachverband Lichtwerbung.



Technical modifications reserved. Content is protected by copyright.

January 2019 EVG-80-1.5-e/01/2019